



UVA(-1) PL-S/PL-L

PL-L 36W/09/4P

Nowadays the preferred phototherapy treatment for skin diseases like psoriasis is done through the use of the 'B' bandwidth of the UV spectrum (290 to 315 nm), since this requires no photo-sensitizing agent. But some patients do not respond to UVB treatment, and for them, phototherapy systems containing UV lamps with an 'A' bandwidth of the UV spectrum are used. These lamps have a wavelength of between 315 to 380 nm.Phillips offers highly reliable T12, PL-S and PL-L lamps emitting this spectral wavelength bandwidth.N.B.: Our UVB lamps are NOT registered with FDA as medical devices as they are NOT packaged or labeled for commercial distribution for health-related purposes. US customers are referred to the UVB and UVA lamp range brochure US version.

Product data

General Information	
Cap-Base	2G11 [2G11]
Main Application	Phototherapy Systems
Life to 50% Failures (Nom)	2000 h
Useful Life (Nom)	1000 h
Light Technical	
Color Code	09
Color Designation	Ultra Violet A
Chromaticity Coordinate X (Nom)	228
Chromaticity Coordinate Y (Nom)	230
UV Depreciation at 500 h	30 %
UV Depreciation at 1000 h	40 %
Operating and Electrical	
Power (Nom)	36 W
Lamp Current (Nom)	0.435 A

Voltage (Nom)	106 V
Mechanical and Housing	
Cap-Base Information	4 Pins
Approval and Application	
Mercury (Hg) Content (Max)	4.9 mg
Mercury (Hg) Content (Nom)	4.4 mg
UV	
UV-A Radiation 100Hr (IEC)	9.0 W
UV-A Radiation OHr (IEC)	10.5 W
Product Data	
Full product code	871150061410040
Order product name	PL-L 36W/09/4P
EAN/UPC - Product	8711500614100

Datasheet, 2018, July 19 data subject to change

UVA(-1) PL-S/PL-L

Order code	927903400907
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927903400907

Net Weight (Piece)	104.000 g	
--------------------	-----------	--

A (max)


39 mm 20.0 mm 384.2 mm 410 mm 416.6 mm

B (max) C (max)

D1 (max) D (max) C1

Warnings and Safety

Dimensional drawing



PL-L 36W/09/4P

Product

PL-L 36W/09/4P 18 mm

